



SML Films Ltd.



SM 701 M

Doc No.-F/PRD/02, Rev.-01, Dt.-01.06.2016

DESCRIPTION : SM 701 M, **Acrylic coated** film is a co-extruded bi-axially oriented polyester film vacuum aluminium metallised on plain side and other side coating.

APPLICATION : Suitable for flexible packaging application, Coating side is suitable for printing.

SALIENT FEATURES :

- High gloss properties.
- Good Water Vapour and Gas Barrier properties.
- Excellent Machineability.
- Good Lamination Adhesion.

TECHNICAL DATA SHEET (SM 701 M)

Properties	Test Method	Unit	SM 701 M								
PHYSICAL											
Thickness	ASTM D-374	Micron	8	10	12	15	19	23	36	50	
Thickness Variation	SMLTM	%	±5	±5	±5	±5	±5	±5	±5	±5	
Average Grammage	SMLTM	g/m ²	11.2	14.0	16.8	21.0	26.6	32.2	50.4	70.0	
Density	ASTM D-1505	g/cc	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	
Metal Bond Strength (Min)	SMLTM	g/25 mm	100	100	100	100	100	100	100	100	
Width	–	mm	510.2450	510.2450	510.2450	510.2450	510.2450	510.2450	510.2450	510.2450	
Length	–	mtr	Up to 48000	Up to 48000	Up to 48000	Up to 36000	Up to 24000	Up to 21000	Up to 18000	Up to 18000	
OPTICAL											
Optical Density	SMLTM	–	2.2 ± 5%	2.2 ± 5%	2.2 ± 5%	2.2 ± 5%	2.2 ± 5%	2.2 ± 5%	2.2 ± 5%	2.2 ± 5%	
MECHANICAL											
Tensile Strength (Min)	MD	ASTM D-882	Kg/cm ²	2300	2300	2300	2200	2200	2200	2100	2000
	TD			2200	2200	2200	2100	2100	2100	2000	2000
Elongation (Min)	MD	ASTM D-882	%	100	100	100	100	100	100	110	120
	TD			90	90	90	90	90	90	100	110
Coefficient of friction (Base Film), (Max)	Static	ASTM D-1894	–	0.50	0.50	0.50	0.50	0.50	0.50	0.50	0.50
	Kinetic			0.45	0.45	0.45	0.45	0.45	0.45	0.45	0.45
THERMAL											
Shrinkage (Max) (150°C / 30 Min)	MD	ASTM D-1204	%	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
	TD			0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
SURFACE											
Wetting Tension	Metal Side	ASTM D-2578	Dyne/cm	54	54	54	54	54	54	54	54
	Coating Side			42	42	42	42	42	42	42	42
BARRIER											
WVTR (38°C & 90% RH) (Max)	ASTM F-1249	g/m ² /day	1.2	1.0	1.0	1.0	1.0	1.0	1.0	1.0	
OTR (23°C & 0% RH) (Max)	ASTM D-3985	cc/m ² /day	1.4	1.2	1.2	1.2	1.2	1.2	1.2	1.2	

SMLTM : SML TEST METHOD, **MD :** MACHINE DIRECTION , **TD :** TRANSVERSE DIRECTION

- Notes:**
- 1- Optical Density up to 2.8 is available on request.
 - 2- Tolerance in width +3mm and -0mm.
 - 3- The above properties are indicative only. Film can be produced to suit customer's requirements.

