



SML Films Ltd.



SM 800 T

Doc No.-F/PRD/02, Rev.-01, Dt.-01.06.2016

DESCRIPTION : SM 800 T, Co-polymer chemically coated film is a co-extruded transparent and corona treated bi-axially oriented polyester film.

APPLICATION : Suitable for printing, lamination, metallization, film specially designed for many flexible packaging applications require high bond strength.

SALIENT FEATURES :

- Good clarity and transparency.
- Excellent adhesion to inks, lacquers & adhesive.
- Excellent metal adhesion when metallized on coated side.
- Excellent mechanical & thermal properties.

TECHNICAL DATA SHEET (SM 800 T)

Properties	Test Method	Unit	SM 800 T								
PHYSICAL											
Thickness	ASTM D-374	Micron	8	10	12	15	19	23	36	50	
Thickness Variation	SMLTM	%	±5	±5	±5	±5	±5	±5	±5	±5	
Average Grammage	SMLTM	g/m ²	11.2	14.0	16.8	21.0	26.6	32.2	50.4	70.0	
Density	ASTM D-1505	g/cc	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	
Width	-	mm	500~3100	500~3100	500~3100	500~3100	500~3100	500~3100	500~3100	500~3100	
Length	-	mtr	Up to 60000	Up to 60000	Up to 60000	Up to 36000	Up to 24000	Up to 21000	Up to 18000	Up to 18000	
Joints	-	%	80% (NIL) 20% (1 Joint)								
OPTICAL											
Haze	ASTM D-1003	%	2.0~3.0	2.0~3.0	2.0~3.0	2.0~3.0	2.0~3.0	2.0~3.0	2.0~3.0	2.0~3.0	
Transmittance	ASTM D-1003	%	88.0~89.0	88.0~89.0	88.0~89.0	88.0~89.0	88.0~89.0	88.0~89.0	88.0~89.0	88.0~89.0	
MECHANICAL											
Tensile Strength (Min)	MD	ASTM D-882	Kg/cm ²	2300	2300	2300	2300	2300	2300	2200	2000
	TD			2200	2200	2200	2200	2200	2200	2200	2200
Elongation (Min)	MD	ASTM D-882	%	100	100	100	100	100	100	120	120
	TD			100	100	100	100	100	100	100	120
Coefficient of friction (Max)	Static	ASTM D-1894	-	0.50	0.50	0.50	0.50	0.50	0.50	0.50	0.50
	Kinetic			0.45	0.45	0.45	0.45	0.45	0.45	0.45	0.45
THERMAL											
Shrinkage (Max) (150°C /30 Min)	MD	ASTM D-1204	%	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
	TD			0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
SURFACE											
Wetting Tension	Coating	ASTM D-2578	Dyne/cm	56	56	56	56	56	56	56	56
	Corona			52-58	52-58	52-58	52-58	52-58	52-58	52-58	52-58

SMLTM :SML TEST METHOD, MD : MACHINE DIRECTION , TD : TRANSVERSE DIRECTION

- Notes:**
- 1- Tolerance in width +3mm and -0mm.
 - 2- The above properties are indicative only. Film can be produced to suit customer's requirements.

